

RZ Medizintechnik GmbH  
Unter Hasslen 20 | D-78532 Tuttlingen  
Phone: +49 (0)7462/9470-0  
Fax: +49 (0)7462/9470-50  
sales@rz-medizintechnik.com  
www.rz-medizintechnik.com



RZ  
Medizintechnik  
GmbH

*Progress in Surgery*

# Manual Xenon Light Sources LUMEN X1 + X3



- | 300-001-180  
LUMEN X 1 Xenon Light Source  
180 Watt
- | 300-001-300  
LUMEN X 3 Xenon Light Source  
300 Watt

08.2013

# HIGH INTENSITY XENON LIGHT SOURCE

Pure daylight quality together with low noise and heat conduction - this Xenon Light Source offers all functions needed to illuminate the field of view. The lamp can be replaced simply.



Manual light intensity control



Pure daylight quality



Lamp lifetime indicator



Easy lamp replacement



300-001-181  
XENON Spare Lamp  
180 Watt

300-001-301  
XENON Spare Lamp  
300 Watt

## TECHNICAL DATA

LUMEN X1 + X3

Lamp	<ul style="list-style-type: none"> <li>Xenon arc lamp</li> <li>300-001-180: 180W</li> <li>300-001-300: 300W</li> <li>Daylight quality 5600 K</li> <li>Lifetime: at least 500h</li> </ul>
Light guide connection	<ul style="list-style-type: none"> <li>RZ/Storz adapter</li> </ul>
System	<ul style="list-style-type: none"> <li>Power supply: 100/240 V/AC, 50-60 Hz</li> <li>Fuses: 2 fine fuses, 5x20mm, delay 6,3 AT (I=1500A)</li> <li>Power consumption: 280Watt/370Watt</li> </ul>
Standard	<ul style="list-style-type: none"> <li>Protection class: I</li> <li>Application part: Type BF</li> <li>IEC 601-1, EN 60601-1; classification acc. 93/42/EEC: I</li> </ul>
Dimensions	<ul style="list-style-type: none"> <li>380 x 120 x 360 mm (WxHxD); 11 kg</li> </ul>
Delivery contains	<ul style="list-style-type: none"> <li>Light source</li> <li>Mains cable</li> </ul>

